

MOVE OVER KNITS THERE'S A NEW WIPE IN TOWN

MICROPOLX® NONWOVEN MICROFIBER TECHNOLOGY

Introducing MicroPolx^{*} nonwoven cleanroom wipes, a first-generation technology featuring a leading edge innovative manufacturing process of 100% polyester microfiber wet-laid nonwoven performance material.


This wiper is a game changer compared to common spunlaced nonwoven options. Available in dry, presaturated, validated sterile, and low endotoxin options, Berkshire's MicroPolx[®] nonwoven microfiber wipers offer a complete line for all your ISO Class 5 and above applications.

TECHNOLOGY	MicroPolx® Nonwoven Microfiber Technology					
ADVANTAGES	 Extremely soft hand Mechanical strength Anti-scratch Multi - directional layering Chemical compatibility Lot to lot traceability 					
RESULTS	Cleans sensitive surfaces without damage while maximizing particle pickup and retention. Superior microfiber contamination removal performance.					

1







MICROFILAMENTS 4.5 TIMES FINER THAN COMMON POLYESTER FILAMENTS FOR SUPERIOR UNIFORMITY



TECHNICAL DATA & ORDER INFORMATION

RECOMMENDED FOR ISO CLASS 5 AND ABOVE APPLICATIONS

BASIS WEIGHT	CALIPER	FIBERS	PARTICLES ≥ 0.5µm	SORBENCY			NON-VOLATILE RESIDUE		IONS (ppm)				
g/m²	μm	≥100µm/cm ²	x10 ³ /cm ²	CAPACITY mL/m ²	EFFICIENCY mL/g	RATE SECONDS	H ₂ O (g/m²)	IPA (g/m²)	Na ⁺	K+	Ca++	Mg⁺⁺	CI
52.2	198	18.8	1.6	234	4.5	6.0	0.0044	0.0040	37	5.3	48	9.3	48

100% polyester microfiber wet-laid nonwoven

DRY WIPER, STACKED 70% IPA/30% DI H2O, 45% AND 60% SATURATION OPTIONS **ITEM NUMBER PRODUCT/ PACKAGING** ITEM NUMBER **PRODUCT/ PACKAGING** MicroPolx® NW - 4x4" (10x10cm) SPXMPNW500112 **MPNW0440** SatPax[®] MP NW – 9x9" (23x23cm) Notes: 400 SHTS /PK, 40 PKS/CS 75 SHTS /PK, 12 PKS/CS Technical data represented in this table are typical values at the time SPXMPNW500112R SatPax[®] MP NW-9x9" (23x23cm) MPNW50090920 MicroPolx[®] NW–9x9" (23x23cm) of publication. These should not be 75 SHTS /PK, 12 PKS/CS 300 SHTS /PK, 20 PKS/CS used as product specifications. · Due to differences in test methods VALIDATED STERILE, 70% IPA/30% DI H2O, 60% SATURATION MPNW50121220 MicroPolx[®] NW - 12x12" (30x30cm) applied and equipment utilized by 150 SHTS /PK, 20 PKS/CS **ITEM NUMBER PRODUCT/ PACKAGING** different wiper manufacturers, valid product comparisons may only be DRY WIPER, VALIDATED STERILE, LOW ENDOTOXIN SSPMPNW500124 Sterile SatPax[®] MP NW – 9x9" (23x23cm) obtained through side-by-side testing in the same test facility, under 30 SHTS /PK, 24 PKS/CS **ITEM NUMBER PRODUCT/ PACKAGING** similar conditions. GWMPNW5ST25LF GammaWipe[®] MP NW - 12x12" (30x30cm) Third party testing can be performed upon request. 20 SHTS /PK, 25 PKS/CS