

### **Product Information**

# ISO Class 5 - 8

Cleanroom Class 100 -100,000 EU Grade A/B/C/D

# Gamma Wipe® Polx® Nonwoven

100% Polyester Nonwoven Cleanroom Wiper

Gamma Wipe® Polx® Nonwoven is a 100% polyester hydroentangled nonwoven wiper recommended for ISO Class 5 and above environments. It is an extremely soft and pliable wiper ideal for all types of sensitive surfaces and an excellent choice for wrapping delicate parts for protection. Additionally, it's critically low fiber and particle generation and minimal non-volatile residues make Gamma Wipe® Polx® Nonwoven an exceptional choice for streak-free cleaning.



#### Other Sterile wipers

- Gamma Wipe SuperSorb®
- Gamma Wipe® 300
- Gamma Wipe® 120
- Gamma Wipe<sup>®</sup> VP
- Gamma Wipe® 67

#### **Key Attributes**

- 100% polyester hydroentangled nonwoven
- No cellulose components, 100% synthetic
- Low fiber and particle generation
- Extremely soft and nonabrasive
- Gamma irradiated and sterile validated to a 10<sup>-6</sup> Sterility Assurance Level per AAMI guidelines
- · Header style packaging with Package Integrity testing
- · Lot tracing on each pack
- Irradiation indicator on each pack and carton
- Certificate of Sterility with each case and available on the web by lot number 24/7. Details: Expiration Date, Radiation Dosage, Lot Information, Meets cGMP requirements for traceability

#### Benefits

- Exceptional cleanliness
- · Chemically compatible with commonly used disinfectants and sporicides
- · Prevents abrasion with its extremely soft and pliable surface
- Works well with IPA and other solvents
- Lot to lot traceability

#### **Applications**

- Designed for use in ISO Class 5 and higher cleanroom environments
- Gentle enough for wiping and polishing soft metal and glass surfaces
- Cleaning of optics and other sensitive surfaces
- · Cleaning and absorbing oil and grease
- Wrapping delicate parts for protection
- Cleaning of lab equipment
- · General equipment wrap and wipe downs

#### www.berkshire.com

Contact: Tel 1 800 242 7000 / 1 413 528 2602 info@berkshire.com

America	Tel 1 413 528 2602	info@berkshire.com
Europe	Tel + 44 1953 562800	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	enquiries@berkshire.com.sg
Japan	Tel 81 3 4530 9883	master@berkshire.co.jp



#### **Technical Data:**

Attribute		Units	Value	Test Method
Basis Weight		g/m²	55.7	TAPPI T-410
Caliper		μm	251	TAPPI T-411
Fibers	≥100µm	fibers/cm <sup>2</sup>	7.4	IEST-RP-CC004.4, Sec 7.1.3 / Sec 7.2.2 modified
Particles	≥0.5µm	x10³/cm²	0.34	IEST-RP-CC004.4, Sec 7.1.3 / Sec 7.2.1 modified
Sorbency	Capacity	mL/m²	261	IEST-RP-CC004.4, Sec 9.1 modified / Sec 9.2 modified
	Efficiency	mL/g	4.7	
	Rate	seconds	2	
Non-Volatile Residue	DI Water	g/m²	0.0020	IEST-RP-CC004.4, Sec 8.1.2
	IPA	g/m²	0.0028	
Ions	Na <sup>+</sup>	ppm	8.9	IEST-RP-CC004.4, Sec 8.2.2
	K <sup>+</sup>	ppm	1.2	
	Ca <sup>++</sup>	ppm	21	
	Mg <sup>++</sup>	ppm	5.0	
	CI-	ppm	11	

#### Notes:

- Technical data represented in this table are typical values at the time of publication. These should not be used as
  product specifications.
- Due to differences in test methods applied and equipment utilized by different wiper manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions
- Third party testing can be performed upon request
- Sorbency capacity, efficiency, and rate performed with 70% IPA

#### **Order Information:**

Product	Number	Size	Shts/pk	Pks/Inner bag	Inner bags/cs	Pks/cs	Style
Gamma Wipe® Polx® Nonwoven	GWPNWST124	12x12"(30x30cm)	25	7	6	42	Header

## Other Berkshire products



**Wipers** 



**Glove Liners** 



**Mop Systems** 



**Documentation Systems** 



**Face Masks** 



Swabs